

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206001

Luminaire Tested: **LD4B10D010 EU4B10209730 4LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206001
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10209730 4LBSB1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 691.7 lumens
Efficiency: N/A
Efficacy: 69.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206001

CATALOG NUMBER: LD4B10D010 EU4B10209730 4LBSB1

Luminous Intensity Polar Plot






TEST NUMBER: P206001

CATALOG NUMBER: LD4B10D010 EU4B10209730 4LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20		
RC	80				70					50					30					10	0	
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10			50	30	10	0
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102				100	
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90				88	
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78				76	
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67				65	
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59				57	
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52				50	
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46				44	
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41				39	
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37				35	
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34				32	
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31				29	

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206001

CATALOG NUMBER: LD4B10D010 EU4B10209730 4LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.8	4.2
10°-20°	81.7	11.8
20°-30°	121.6	17.6
30°-40°	141.4	20.4
40°-50°	137.9	19.9
50°-60°	106.0	15.3
60°-70°	58.6	8.5
70°-80°	15.5	2.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	232.1	33.6
0°-40°	373.5	54.0
0°-60°	617.4	89.3
0°-90°	691.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	691.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	305	
5°	303	29
15°	289	82
25°	264	122
35°	227	141
45°	179	138
55°	118	106
65°	59	59
75°	13	16
85°	0	0
90°	0	



TEST NUMBER: P206001

CATALOG NUMBER: LD4B10D010 EU4B10209730 4LBSB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	305.1
2.5°	305.1
5°	303.4
7.5°	300.8
10°	299.0
12.5°	293.7
15°	289.4
17.5°	285.0
20°	278.8
22.5°	272.7
25°	263.9
27.5°	255.2
30°	246.4
32.5°	236.7
35°	227.1
37.5°	214.8
40°	204.3
42.5°	192.9
45°	178.9
47.5°	165.7
50°	150.8
52.5°	135.0
55°	118.4
57.5°	102.6
60°	87.7
62.5°	72.8
65°	58.7
67.5°	45.6
70°	33.3
72.5°	22.8
75°	13.2
77.5°	6.1
80°	0.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)