

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755219

Luminaire Tested: LD4D85BD010-EU4DR7070959035-4LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P755219
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D85BD010-EU4DR7070959035-4LBSQW1B
Description: 4 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5104.9 lumens
Efficiency: N/A
Efficacy: 58.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P755219
CATALOG NUMBER: LD4D85BD010-EU4DR7070959035-4LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P755219

CATALOG NUMBER: LD4D85BD010-EU4DR7070959035-4LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	627080
5°	608450
10°	591488
15°	583730
20°	545087
25°	409492
30°	289482
35°	102545
40°	53914
45°	57434
50°	59459
55°	60576
60°	60968
65°	59669
70°	56320
75°	52178
80°	46310
85°	37609

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 60985 cd/sqm



TEST NUMBER: P755219

CATALOG NUMBER: LD4D85BD010-EU4DR7070959035-4LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	523.3	10.3
10°-20°	1435.3	28.1
20°-30°	1580.8	31.0
30°-40°	604.0	11.8
40°-50°	285.2	5.6
50°-60°	283.5	5.6
60°-70°	227.0	4.4
70°-80°	130.5	2.6
80°-90°	35.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3539.3	69.3
0°-40°	4143.3	81.2
0°-60°	4712.0	92.3
0°-90°	5104.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5104.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5739	
5°	5548	523
15°	5160	1435
25°	3397	1581
35°	769	604
45°	372	285
55°	318	284
65°	231	227
75°	124	130
85°	30	35
90°	0	



TEST NUMBER: P755219

CATALOG NUMBER: LD4D85BD010-EU4DR7070959035-4LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	5739.3
2.5°	5679.4
5°	5547.6
7.5°	5437.6
10°	5331.3
12.5°	5241.4
15°	5160.5
17.5°	4965.1
20°	4688.0
22.5°	4090.1
25°	3396.7
27.5°	2956.9
30°	2294.5
32.5°	1482.1
35°	768.8
37.5°	415.3
40°	378.0
42.5°	375.3
45°	371.7
47.5°	363.5
50°	349.8
52.5°	334.4
55°	318.0
57.5°	299.9
60°	279.0
62.5°	255.3
65°	230.8
67.5°	203.5
70°	176.3
72.5°	149.0
75°	123.6
77.5°	97.2
80°	73.6
82.5°	51.8
85°	30.0
87.5°	11.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)