

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755077

Luminaire Tested: LD4D85BD010-EU4DR6070959040-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P755077
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D85BD010-EU4DR6070959040-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7725.4 lumens
Efficiency: N/A
Efficacy: 88.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P755077
CATALOG NUMBER: LD4D85BD010-EU4DR6070959040-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P755077

CATALOG NUMBER: LD4D85BD010-EU4DR6070959040-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1002456
5°	1027103
10°	1039511
15°	990277
20°	873116
25°	706204
30°	477680
35°	239369
40°	38824
45°	38011
50°	38772
55°	39355
60°	40448
65°	41365
70°	42328
75°	42848
80°	41339
85°	34475

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 42848 cd/sqm



TEST NUMBER: P755077

CATALOG NUMBER: LD4D85BD010-EU4DR6070959040-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	895.0	11.6
10°-20°	2421.6	31.3
20°-30°	2605.4	33.7
30°-40°	1132.5	14.7
40°-50°	190.2	2.5
50°-60°	185.0	2.4
60°-70°	158.2	2.0
70°-80°	105.9	1.4
80°-90°	31.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5922.0	76.7
0°-40°	7054.5	91.3
0°-60°	7429.7	96.2
0°-90°	7725.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7725.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9175	
5°	9365	895
15°	8755	2422
25°	5858	2605
35°	1795	1133
45°	246	190
55°	207	185
65°	160	158
75°	102	106
85°	28	32
90°	0	



TEST NUMBER: P755077

CATALOG NUMBER: LD4D85BD010-EU4DR6070959040-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	9174.9
2.5°	9432.8
5°	9364.7
7.5°	9386.2
10°	9369.5
12.5°	9176.1
15°	8754.6
17.5°	8188.6
20°	7509.2
22.5°	6782.0
25°	5857.9
27.5°	4685.3
30°	3786.2
32.5°	2918.2
35°	1794.6
37.5°	767.8
40°	272.2
42.5°	250.7
45°	246.0
47.5°	237.6
50°	228.1
52.5°	217.3
55°	206.6
57.5°	195.8
60°	185.1
62.5°	173.1
65°	160.0
67.5°	146.9
70°	132.5
72.5°	117.0
75°	101.5
77.5°	83.6
80°	65.7
82.5°	46.6
85°	27.5
87.5°	9.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)