

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755155

Luminaire Tested: LD4D85BD010-EU4DR6570959040-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P755155
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D85BD010-EU4DR6570959040-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6755.8 lumens
Efficiency: N/A
Efficacy: 77.0 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P755155

CATALOG NUMBER: LD4D85BD010-EU4DR6570959040-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P755155
 CATALOG NUMBER: LD4D85BD010-EU4DR6570959040-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	726759
5°	727352
10°	752959
15°	754206
20°	694370
25°	591640
30°	452927
35°	319985
40°	188885
45°	76672
50°	27792
55°	15487
60°	8872
65°	4886
70°	5143
75°	4010
80°	4153
85°	3510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 76672 cd/sqm



TEST NUMBER: P755155

CATALOG NUMBER: LD4D85BD010-EU4DR6570959040-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	640.5	9.5
10°-20°	1847.5	27.3
20°-30°	2216.7	32.8
30°-40°	1489.7	22.1
40°-50°	445.9	6.6
50°-60°	78.7	1.2
60°-70°	22.4	0.3
70°-80°	11.0	0.2
80°-90°	3.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4704.7	69.6
0°-40°	6194.3	91.7
0°-60°	6719.0	99.5
0°-90°	6755.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6755.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6652	
5°	6632	640
15°	6668	1848
25°	4908	2217
35°	2399	1490
45°	496	446
55°	81	79
65°	19	22
75°	10	11
85°	3	3
90°	0	



TEST NUMBER: P755155

CATALOG NUMBER: LD4D85BD010-EU4DR6570959040-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	6651.6
2.5°	6679.9
5°	6631.7
7.5°	6731.9
10°	6786.7
12.5°	6773.5
15°	6667.6
17.5°	6408.6
20°	5971.9
22.5°	5457.7
25°	4907.6
27.5°	4286.6
30°	3590.0
32.5°	2958.6
35°	2399.0
37.5°	1846.0
40°	1324.3
42.5°	864.9
45°	496.2
47.5°	262.8
50°	163.5
52.5°	113.4
55°	81.3
57.5°	58.6
60°	40.6
62.5°	26.5
65°	18.9
67.5°	17.0
70°	16.1
72.5°	12.3
75°	9.5
77.5°	8.5
80°	6.6
82.5°	4.7
85°	2.8
87.5°	1.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)