

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207334

Luminaire Tested: **LD4B10D010 EU4B10208035 4LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207334
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10208035 4LBMGPH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 594.0 lumens
Efficiency: N/A
Efficacy: 60.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.92
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207334

CATALOG NUMBER: LD4B10D010 EU4B10208035 4LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P207334

CATALOG NUMBER: LD4B10D010 EU4B10208035 4LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93																																				
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	88	86																																				
3	102	95	90	86	100	93	89	85	91	87	83	88	85	82	86	83	81	79																																				
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73																																				
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68																																				
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63																																				
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59																																				
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55																																				
9	73	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	52	51																																				
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207334

CATALOG NUMBER: LD4B10D010 EU4B10208035 4LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.2	9.5
10°-20°	146.5	24.7
20°-30°	188.0	31.6
30°-40°	135.9	22.9
40°-50°	48.7	8.2
50°-60°	13.1	2.2
60°-70°	4.3	0.7
70°-80°	1.3	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	390.7	65.8
0°-40°	526.6	88.7
0°-60°	588.4	99.1
0°-90°	594.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	594.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	611	
5°	600	56
15°	522	147
25°	415	188
35°	217	136
45°	59	49
55°	14	13
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P207334

CATALOG NUMBER: LD4B10D010 EU4B10208035 4LBMGPH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	610.7
2.5°	608.2
5°	599.5
7.5°	585.7
10°	567.0
12.5°	545.8
15°	522.0
17.5°	498.3
20°	474.6
22.5°	447.1
25°	414.6
27.5°	377.2
30°	329.7
32.5°	274.8
35°	217.3
37.5°	164.9
40°	119.9
42.5°	84.9
45°	58.7
47.5°	40.0
50°	26.2
52.5°	18.7
55°	13.7
57.5°	10.0
60°	7.5
62.5°	6.2
65°	3.7
67.5°	2.5
70°	2.5
72.5°	1.2
75°	1.2
77.5°	1.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)