

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755233

Luminaire Tested: LD4D85BD010-EU4DR7070959040-4LBSQW1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P755233  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D85BD010-EU4DR7070959040-4LBSQW1MW  
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7116.7 lumens  
Efficiency: N/A  
Efficacy: 81.1 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 87.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P755233  
CATALOG NUMBER: LD4D85BD010-EU4DR7070959040-4LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P755233  
 CATALOG NUMBER: LD4D85BD010-EU4DR7070959040-4LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	874217
5°	848240
10°	824597
15°	813772
20°	759901
25°	570880
30°	403559
35°	142946
40°	75166
45°	80056
50°	82899
55°	84463
60°	84983
65°	83196
70°	78523
75°	72737
80°	64557
85°	52402

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 85001 cd/sqm



TEST NUMBER: P755233

CATALOG NUMBER: LD4D85BD010-EU4DR7070959040-4LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	729.5	10.3
10°-20°	2000.9	28.1
20°-30°	2203.7	31.0
30°-40°	842.0	11.8
40°-50°	397.6	5.6
50°-60°	395.2	5.6
60°-70°	316.5	4.4
70°-80°	181.9	2.6
80°-90°	49.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4934.1	69.3
0°-40°	5776.1	81.2
0°-60°	6568.9	92.3
0°-90°	7116.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7116.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8001	
5°	7734	729
15°	7194	2001
25°	4735	2204
35°	1072	842
45°	518	398
55°	443	395
65°	322	316
75°	172	182
85°	42	49
90°	0	



TEST NUMBER: P755233

CATALOG NUMBER: LD4D85BD010-EU4DR7070959040-4LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8001.2
2.5°	7917.6
5°	7733.9
7.5°	7580.6
10°	7432.4
12.5°	7307.0
15°	7194.2
17.5°	6921.9
20°	6535.5
22.5°	5701.9
25°	4735.4
27.5°	4122.2
30°	3198.7
32.5°	2066.2
35°	1071.7
37.5°	578.9
40°	527.0
42.5°	523.2
45°	518.1
47.5°	506.7
50°	487.7
52.5°	466.2
55°	443.4
57.5°	418.0
60°	388.9
62.5°	356.0
65°	321.8
67.5°	283.8
70°	245.8
72.5°	207.8
75°	172.3
77.5°	135.5
80°	102.6
82.5°	72.2
85°	41.8
87.5°	16.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)