

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206613

Luminaire Tested: **LD4B10D010 EU4B10208035 4LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206613
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10208035 4LBWH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 919.7 lumens
Efficiency: N/A
Efficacy: 92.9 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206613

CATALOG NUMBER: LD4B10D010 EU4B10208035 4LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P206613

CATALOG NUMBER: LD4B10D010 EU4B10208035 4LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206613

CATALOG NUMBER: LD4B10D010 EU4B10208035 4LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.5	6.1
10°-20°	162.7	17.7
20°-30°	240.1	26.1
30°-40°	236.9	25.8
40°-50°	145.0	15.8
50°-60°	55.6	6.0
60°-70°	17.4	1.9
70°-80°	5.1	0.6
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	459.2	49.9
0°-40°	696.1	75.7
0°-60°	896.6	97.5
0°-90°	919.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	919.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	593	
5°	593	56
15°	577	163
25°	525	240
35°	384	237
45°	186	145
55°	59	56
65°	16	17
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P206613

CATALOG NUMBER: LD4B10D010 EU4B10208035 4LBWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	592.8
2.5°	594.1
5°	592.8
7.5°	591.6
10°	587.8
12.5°	582.8
15°	576.6
17.5°	569.1
20°	557.9
22.5°	545.4
25°	525.4
27.5°	500.5
30°	469.3
32.5°	430.6
35°	384.4
37.5°	333.2
40°	280.8
42.5°	232.1
45°	186.0
47.5°	144.8
50°	109.8
52.5°	81.1
55°	58.7
57.5°	41.2
60°	30.0
62.5°	22.5
65°	16.2
67.5°	12.5
70°	8.7
72.5°	6.2
75°	5.0
77.5°	2.5
80°	2.5
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)