

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206721

Luminaire Tested: **LD4B10D010 EU4B10209035 4LBWWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206721  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B10D010 EU4B10209035 4LBWWH1  
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W  
DL3-11.1W DLE-11.39W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 807.6 lumens  
Efficiency: N/A  
Efficacy: 81.6 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206721

CATALOG NUMBER: LD4B10D010 EU4B10209035 4LBWWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P206721

CATALOG NUMBER: LD4B10D010 EU4B10209035 4LBWWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	87	85	84	84	84	84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76	76	76	76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69	69	69	69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63	63	63	63
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58	58	58	58
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53	53	53	53
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49	49	49	49
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45	45	45	45
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41	41	41	41

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206721

CATALOG NUMBER: LD4B10D010 EU4B10209035 4LBWWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	48.9	6.1
10°-20°	151.3	18.7
20°-30°	232.8	28.8
30°-40°	224.6	27.8
40°-50°	117.1	14.5
50°-60°	24.6	3.1
60°-70°	5.7	0.7
70°-80°	2.2	0.3
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	433.1	53.6
0°-40°	657.7	81.4
0°-60°	799.4	99.0
0°-90°	807.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	807.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	505	
5°	509	49
15°	536	151
25°	510	233
35°	364	225
45°	149	117
55°	22	25
65°	5	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P206721

CATALOG NUMBER: LD4B10D010 EU4B10209035 4LBWWH1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	504.9
2.5°	506.0
5°	509.1
7.5°	513.4
10°	519.7
12.5°	528.1
15°	535.5
17.5°	539.8
20°	536.6
22.5°	530.3
25°	510.2
27.5°	485.9
30°	454.2
32.5°	412.0
35°	364.4
37.5°	312.7
40°	258.8
42.5°	204.9
45°	148.9
47.5°	100.3
50°	64.4
52.5°	39.1
55°	22.2
57.5°	13.7
60°	9.5
62.5°	7.4
65°	5.3
67.5°	4.2
70°	3.2
72.5°	3.2
75°	2.1
77.5°	1.1
80°	1.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)