

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P252053

Luminaire Tested: **LD4B10D010 EU4B10208040 4LBBA1MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P252053
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-4)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10208040 4LBBA1MB
Description: PORTFOLIO 4 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE BLACK TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 556.0 lumens
Efficiency: N/A
Efficacy: 55.3 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 0.94
Luminous Opening: Circular (Dia: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 10.05
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P252053

CATALOG NUMBER: LD4B10D010 EU4B10208040 4LBBA1MB

Luminous Intensity Polar Plot





TEST NUMBER: P252053

CATALOG NUMBER: LD4B10D010 EU4B10208040 4LBBA1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	88	83	79	86	82	78	84	81	77	82	79	77	75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65			
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61			
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58	57			
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			
10	72	62	56	52	71	61	56	52	60	55	52	60	55	52	59	55	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	54196
5°	54041
10°	53518
15°	52658
20°	51120
25°	47229
30°	38318
35°	23747
40°	11170
45°	3900
50°	1107
55°	748
60°	565
65°	507
70°	427
75°	264
80°	393
85°	0



TEST NUMBER: P252053

CATALOG NUMBER: LD4B10D010 EU4B10208040 4LBBA1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.4	9.4
10°-20°	146.7	26.4
20°-30°	197.2	35.5
30°-40°	126.0	22.7
40°-50°	26.8	4.8
50°-60°	4.0	0.7
60°-70°	2.0	0.4
70°-80°	0.8	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	396.3	71.3
0°-40°	522.2	93.9
0°-60°	553.1	99.5
0°-90°	556.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	556.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	556	
5°	552	52
15°	522	147
25°	439	197
35°	200	126
45°	28	27
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P252053

CATALOG NUMBER: LD4B10D010 EU4B10208040 4LBBA1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	556.1
2.5°	555.3
5°	552.4
7.5°	547.3
10°	540.8
12.5°	532.1
15°	521.9
17.5°	508.9
20°	492.9
22.5°	470.4
25°	439.2
27.5°	395.6
30°	340.5
32.5°	272.2
35°	199.6
37.5°	136.5
40°	87.8
42.5°	52.3
45°	28.3
47.5°	14.5
50°	7.3
52.5°	5.1
55°	4.4
57.5°	3.6
60°	2.9
62.5°	2.2
65°	2.2
67.5°	1.5
70°	1.5
72.5°	0.7
75°	0.7
77.5°	0.7
80°	0.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)