

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206614

Luminaire Tested: **LD4B10D010 EU4B10208040 4LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206614
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10208040 4LBWH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 929.8 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206614

CATALOG NUMBER: LD4B10D010 EU4B10208040 4LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P206614

CATALOG NUMBER: LD4B10D010 EU4B10208040 4LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206614

CATALOG NUMBER: LD4B10D010 EU4B10208040 4LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.1	6.1
10°-20°	164.5	17.7
20°-30°	242.7	26.1
30°-40°	239.5	25.8
40°-50°	146.6	15.8
50°-60°	56.2	6.0
60°-70°	17.5	1.9
70°-80°	5.1	0.6
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	464.2	49.9
0°-40°	703.7	75.7
0°-60°	906.4	97.5
0°-90°	929.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	929.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	599	
5°	599	57
15°	583	164
25°	531	243
35°	389	239
45°	188	147
55°	59	56
65°	16	18
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P206614

CATALOG NUMBER: LD4B10D010 EU4B10208040 4LBWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	599.3
2.5°	600.6
5°	599.3
7.5°	598.1
10°	594.3
12.5°	589.2
15°	582.9
17.5°	575.3
20°	564.0
22.5°	551.4
25°	531.2
27.5°	505.9
30°	474.4
32.5°	435.3
35°	388.6
37.5°	336.9
40°	283.9
42.5°	234.7
45°	188.0
47.5°	146.4
50°	111.0
52.5°	82.0
55°	59.3
57.5°	41.6
60°	30.3
62.5°	22.7
65°	16.4
67.5°	12.6
70°	8.8
72.5°	6.3
75°	5.0
77.5°	2.5
80°	2.5
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)