

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755885

Luminaire Tested: LD4D90BD010-EU4DR6570959027-4LBCSSQMMS

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P755885  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D90BD010-EU4DR6570959027-4LBCSSQMMMS  
Description: 4 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7341.5 lumens  
Efficiency: N/A  
Efficacy: 74.2 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct

Input Watts (W): 98.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P755885  
CATALOG NUMBER: LD4D90BD010-EU4DR6570959027-4LBCSSQMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P755885  
 CATALOG NUMBER: LD4D90BD010-EU4DR6570959027-4LBCSSQMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	389309
5°	388327
10°	387996
15°	376039
20°	342334
25°	298326
30°	248121
35°	196597
40°	141892
45°	89641
50°	46729
55°	24835
60°	13047
65°	7172
70°	3005
75°	3317
80°	2321
85°	1943

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 89641 cd/sqm



TEST NUMBER: P755885

CATALOG NUMBER: LD4D90BD010-EU4DR6570959027-4LBCSSQMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	630.4	8.6
10°-20°	1726.2	23.5
20°-30°	2110.0	28.7
30°-40°	1712.0	23.3
40°-50°	853.1	11.6
50°-60°	238.0	3.2
60°-70°	54.1	0.7
70°-80°	14.1	0.2
80°-90°	3.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4466.6	60.8
0°-40°	6178.6	84.2
0°-60°	7269.7	99.0
0°-90°	7341.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7341.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6666	
5°	6624	630
15°	6219	1726
25°	4629	2110
35°	2757	1712
45°	1085	853
55°	244	238
65°	52	54
75°	15	14
85°	3	4
90°	0	



TEST NUMBER: P755885

CATALOG NUMBER: LD4D90BD010-EU4DR6570959027-4LBCSSQMMMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6665.8
2.5°	6660.9
5°	6623.7
7.5°	6602.2
10°	6542.4
12.5°	6421.0
15°	6219.2
17.5°	5903.7
20°	5508.0
22.5°	5080.9
25°	4629.4
27.5°	4146.4
30°	3679.2
32.5°	3217.8
35°	2757.4
37.5°	2298.0
40°	1861.1
42.5°	1451.7
45°	1085.3
47.5°	756.2
50°	514.3
52.5°	354.6
55°	243.9
57.5°	164.6
60°	111.7
62.5°	77.4
65°	51.9
67.5°	26.4
70°	17.6
72.5°	16.7
75°	14.7
77.5°	9.8
80°	6.9
82.5°	4.9
85°	2.9
87.5°	2.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)