

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206414

Luminaire Tested: **LD4B10D010 EU4B10209040 4LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206414
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10209040 4LBCSMB1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 910.2 lumens
Efficiency: N/A
Efficacy: 91.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206414

CATALOG NUMBER: LD4B10D010 EU4B10209040 4LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P206414

CATALOG NUMBER: LD4B10D010 EU4B10209040 4LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88	88	88	88
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75	75	75	75
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65	65	65	65
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56	56	56	56
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49	49	49	49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43	43	43	43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39	39	39	39
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35	35	35	35
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31	31	31	31
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28	28	28	28

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206414

CATALOG NUMBER: LD4B10D010 EU4B10209040 4LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.4	4.0
10°-20°	103.6	11.4
20°-30°	155.7	17.1
30°-40°	184.7	20.3
40°-50°	182.8	20.1
50°-60°	143.6	15.8
60°-70°	80.5	8.8
70°-80°	22.6	2.5
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	295.6	32.5
0°-40°	480.3	52.8
0°-60°	806.7	88.6
0°-90°	910.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	910.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	384	
5°	384	36
15°	367	104
25°	338	156
35°	296	185
45°	238	183
55°	162	144
65°	80	81
75°	20	23
85°	0	0
90°	0	



TEST NUMBER: P206414

CATALOG NUMBER: LD4B10D010 EU4B10209040 4LBCSMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	384.3
2.5°	383.0
5°	383.7
7.5°	380.4
10°	376.5
12.5°	371.9
15°	367.3
17.5°	361.5
20°	353.6
22.5°	345.8
25°	338.0
27.5°	329.5
30°	318.4
32.5°	307.3
35°	296.2
37.5°	283.2
40°	268.2
42.5°	253.8
45°	238.2
47.5°	220.5
50°	202.3
52.5°	181.4
55°	161.8
57.5°	139.6
60°	118.8
62.5°	99.8
65°	80.3
67.5°	63.3
70°	47.0
72.5°	32.0
75°	19.6
77.5°	9.8
80°	2.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)