

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206305

Luminaire Tested: **LD4B10D010 EU4B10208050 4LBCSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206305  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B10D010 EU4B10208050 4LBCSMW1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM  
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W  
DL3-11.1W DLE-11.39W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1160.6 lumens  
Efficiency: N/A  
Efficacy: 117.2 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206305

CATALOG NUMBER: LD4B10D010 EU4B10208050 4LBCSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P206305

CATALOG NUMBER: LD4B10D010 EU4B10208050 4LBCSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87	87	87	87
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74	74	74	74
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63	63	63	63
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55	55	55	55
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48	48	48	48
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42	42	42	42
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37	37	37	37
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33	33	33	33
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30	30	30	30
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27	27	27	27

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206305

CATALOG NUMBER: LD4B10D010 EU4B10208050 4LBCSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.9	3.9
10°-20°	127.9	11.0
20°-30°	192.4	16.6
30°-40°	228.0	19.6
40°-50°	226.9	19.5
50°-60°	182.9	15.8
60°-70°	110.6	9.5
70°-80°	41.1	3.5
80°-90°	6.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	365.1	31.5
0°-40°	593.1	51.1
0°-60°	1002.8	86.4
0°-90°	1160.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1160.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	474	
5°	472	45
15°	453	128
25°	418	192
35°	365	228
45°	295	227
55°	204	183
65°	111	111
75°	37	41
85°	5	6
90°	0	



TEST NUMBER: P206305

CATALOG NUMBER: LD4B10D010 EU4B10208050 4LBCSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	474.0
2.5°	474.0
5°	471.9
7.5°	470.5
10°	466.3
12.5°	459.3
15°	452.9
17.5°	445.9
20°	437.5
22.5°	429.0
25°	417.8
27.5°	405.8
30°	392.5
32.5°	379.8
35°	365.0
37.5°	349.6
40°	331.3
42.5°	313.7
45°	295.4
47.5°	275.0
50°	252.5
52.5°	229.3
55°	204.0
57.5°	181.5
60°	156.1
62.5°	133.6
65°	111.1
67.5°	90.0
70°	70.3
72.5°	52.7
75°	37.3
77.5°	23.9
80°	14.1
82.5°	8.4
85°	4.9
87.5°	2.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)