

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756000

Luminaire Tested: LD4D90BD010-EU4DR7070959035-4LBSQW1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P756000  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D90BD010-EU4DR7070959035-4LBSQW1MW  
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7212.7 lumens  
Efficiency: N/A  
Efficacy: 72.9 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 98.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P756000

CATALOG NUMBER: LD4D90BD010-EU4DR7070959035-4LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P756000

CATALOG NUMBER: LD4D90BD010-EU4DR7070959035-4LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	886006
5°	859679
10°	835714
15°	824744
20°	770145
25°	578572
30°	408997
35°	144880
40°	76179
45°	81137
50°	84021
55°	85606
60°	86141
65°	84308
70°	79577
75°	73708
80°	65438
85°	53154

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 86160 cd/sqm



TEST NUMBER: P756000

CATALOG NUMBER: LD4D90BD010-EU4DR7070959035-4LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	739.3	10.3
10°-20°	2027.9	28.1
20°-30°	2233.4	31.0
30°-40°	853.3	11.8
40°-50°	402.9	5.6
50°-60°	400.6	5.6
60°-70°	320.7	4.4
70°-80°	184.3	2.6
80°-90°	50.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5000.6	69.3
0°-40°	5854.0	81.2
0°-60°	6657.5	92.3
0°-90°	7212.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7212.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8109	
5°	7838	739
15°	7291	2028
25°	4799	2233
35°	1086	853
45°	525	403
55°	449	401
65°	326	321
75°	175	184
85°	42	50
90°	0	



TEST NUMBER: P756000

CATALOG NUMBER: LD4D90BD010-EU4DR7070959035-4LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8109.1
2.5°	8024.3
5°	7838.2
7.5°	7682.8
10°	7532.6
12.5°	7405.5
15°	7291.2
17.5°	7015.2
20°	6623.6
22.5°	5778.8
25°	4799.2
27.5°	4177.8
30°	3241.8
32.5°	2094.0
35°	1086.2
37.5°	586.7
40°	534.1
42.5°	530.2
45°	525.1
47.5°	513.6
50°	494.3
52.5°	472.5
55°	449.4
57.5°	423.7
60°	394.2
62.5°	360.8
65°	326.1
67.5°	287.6
70°	249.1
72.5°	210.6
75°	174.6
77.5°	137.4
80°	104.0
82.5°	73.2
85°	42.4
87.5°	16.7
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)