

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207547

Luminaire Tested: **LD4B10D010 EU4B10209050 4LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207547
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10209050 4LBMMW1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 732.1 lumens
Efficiency: N/A
Efficacy: 74.0 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207547

CATALOG NUMBER: LD4B10D010 EU4B10209050 4LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P207547

CATALOG NUMBER: LD4B10D010 EU4B10209050 4LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89		
2	104	98	92	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80		
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71		
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	69	66	64		
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58		
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53		
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49		
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45		
9	67	55	48	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42		
10	63	52	45	41	62	51	45	41	51	45	40	50	44	40	49	44	40	39		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207547

CATALOG NUMBER: LD4B10D010 EU4B10209050 4LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.5	7.0
10°-20°	138.1	18.9
20°-30°	183.6	25.1
30°-40°	150.2	20.5
40°-50°	87.5	11.9
50°-60°	58.0	7.9
60°-70°	38.2	5.2
70°-80°	20.1	2.7
80°-90°	4.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	373.3	51.0
0°-40°	523.5	71.5
0°-60°	669.0	91.4
0°-90°	732.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	732.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	556	
5°	549	52
15°	492	138
25°	403	184
35°	240	150
45°	110	87
55°	65	58
65°	38	38
75°	19	20
85°	4	5
90°	0	



TEST NUMBER: P207547

CATALOG NUMBER: LD4B10D010 EU4B10209050 4LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	555.8
2.5°	554.7
5°	549.4
7.5°	536.7
10°	522.9
12.5°	510.2
15°	492.1
17.5°	472.0
20°	455.0
22.5°	431.7
25°	403.1
27.5°	372.3
30°	333.0
32.5°	286.4
35°	239.7
37.5°	197.3
40°	160.2
42.5°	131.5
45°	110.3
47.5°	93.3
50°	81.7
52.5°	72.1
55°	64.7
57.5°	57.3
60°	49.9
62.5°	44.5
65°	38.2
67.5°	32.9
70°	27.6
72.5°	23.3
75°	19.1
77.5°	14.8
80°	10.6
82.5°	7.4
85°	4.2
87.5°	1.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)