

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207032

Luminaire Tested: **LD4B10D010 EU4B10209050 4LBWMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P207032  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B10D010 EU4B10209050 4LBWMW1  
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W  
DL3-11.1W DLE-11.39W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 817.0 lumens  
Efficiency: N/A  
Efficacy: 82.5 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P207032

CATALOG NUMBER: LD4B10D010 EU4B10209050 4LBWMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P207032

CATALOG NUMBER: LD4B10D010 EU4B10209050 4LBWMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78			
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69			
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61			
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55			
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	60	55	51	50			
7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45			
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41			
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38			
10	61	49	42	37	59	48	41	37	47	41	37	46	41	37	46	40	36	35			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P207032

CATALOG NUMBER: LD4B10D010 EU4B10209050 4LBWMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	46.5	5.7
10°-20°	130.0	15.9
20°-30°	183.7	22.5
30°-40°	178.0	21.8
40°-50°	120.1	14.7
50°-60°	74.5	9.1
60°-70°	49.8	6.1
70°-80°	27.2	3.3
80°-90°	7.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	360.2	44.1
0°-40°	538.1	65.9
0°-60°	732.8	89.7
0°-90°	817.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	817.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	495	
5°	491	46
15°	461	130
25°	403	184
35°	286	178
45°	154	120
55°	82	75
65°	50	50
75°	25	27
85°	6	7
90°	0	



TEST NUMBER: P207032

CATALOG NUMBER: LD4B10D010 EU4B10209050 4LBWMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	495.1
2.5°	495.1
5°	490.9
7.5°	485.6
10°	479.2
12.5°	472.8
15°	461.2
17.5°	451.6
20°	435.7
22.5°	419.8
25°	402.9
27.5°	379.5
30°	354.1
32.5°	321.2
35°	286.2
37.5°	251.3
40°	216.3
42.5°	181.3
45°	153.7
47.5°	128.3
50°	109.2
52.5°	93.3
55°	81.6
57.5°	72.1
60°	64.7
62.5°	57.2
65°	49.8
67.5°	43.5
70°	37.1
72.5°	31.8
75°	25.4
77.5°	20.1
80°	14.8
82.5°	10.6
85°	6.4
87.5°	2.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)