

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756013

Luminaire Tested: LD4D90BD010-EU4DR7070959040-4LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P756013
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D90BD010-EU4DR7070959040-4LBSQW1MW
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7549.9 lumens
Efficiency: N/A
Efficacy: 76.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 98.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P756013

CATALOG NUMBER: LD4D90BD010-EU4DR7070959040-4LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P756013

CATALOG NUMBER: LD4D90BD010-EU4DR7070959040-4LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	927427
5°	899865
10°	874789
15°	863305
20°	806155
25°	605625
30°	428123
35°	151656
40°	79744
45°	84939
50°	87947
55°	89607
60°	90162
65°	88263
70°	83282
75°	77169
80°	68521
85°	55536

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 90186 cd/sqm



TEST NUMBER: P756013

CATALOG NUMBER: LD4D90BD010-EU4DR7070959040-4LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	773.9	10.3
10°-20°	2122.7	28.1
20°-30°	2337.9	31.0
30°-40°	893.2	11.8
40°-50°	421.8	5.6
50°-60°	419.3	5.6
60°-70°	335.7	4.4
70°-80°	193.0	2.6
80°-90°	52.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5234.4	69.3
0°-40°	6127.7	81.2
0°-60°	6968.8	92.3
0°-90°	7549.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7549.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8488	
5°	8205	774
15°	7632	2123
25°	5024	2338
35°	1137	893
45°	550	422
55°	470	419
65°	341	336
75°	183	193
85°	44	52
90°	0	



TEST NUMBER: P756013

CATALOG NUMBER: LD4D90BD010-EU4DR7070959040-4LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	8488.2
2.5°	8399.5
5°	8204.6
7.5°	8042.0
10°	7884.8
12.5°	7751.7
15°	7632.1
17.5°	7343.2
20°	6933.3
22.5°	6049.0
25°	5023.6
27.5°	4373.1
30°	3393.4
32.5°	2191.9
35°	1137.0
37.5°	614.2
40°	559.1
42.5°	555.0
45°	549.7
47.5°	537.6
50°	517.4
52.5°	494.6
55°	470.4
57.5°	443.5
60°	412.6
62.5°	377.6
65°	341.4
67.5°	301.0
70°	260.7
72.5°	220.4
75°	182.8
77.5°	143.8
80°	108.9
82.5°	76.6
85°	44.3
87.5°	17.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)