

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206625

Luminaire Tested: **LD4B15D010 EU4B10208035 4LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206625
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10208035 4LBWH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1281.1 lumens
Efficiency: N/A
Efficacy: 89.6 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206625

CATALOG NUMBER: LD4B15D010 EU4B10208035 4LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P206625

CATALOG NUMBER: LD4B15D010 EU4B10208035 4LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82		
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67		
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61		
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55		
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50		
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46		
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43		
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206625

CATALOG NUMBER: LD4B15D010 EU4B10208035 4LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.6	6.1
10°-20°	226.6	17.7
20°-30°	334.4	26.1
30°-40°	330.0	25.8
40°-50°	201.9	15.8
50°-60°	77.4	6.0
60°-70°	24.2	1.9
70°-80°	7.1	0.6
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	639.6	49.9
0°-40°	969.6	75.7
0°-60°	1248.9	97.5
0°-90°	1281.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1281.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	826	
5°	826	79
15°	803	227
25°	732	334
35°	535	330
45°	259	202
55°	82	77
65°	23	24
75°	7	7
85°	0	1
90°	0	



TEST NUMBER: P206625

CATALOG NUMBER: LD4B15D010 EU4B10208035 4LBWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	825.7
2.5°	827.5
5°	825.7
7.5°	824.0
10°	818.8
12.5°	811.8
15°	803.1
17.5°	792.7
20°	777.1
22.5°	759.7
25°	731.9
27.5°	697.1
30°	653.6
32.5°	599.8
35°	535.4
37.5°	464.2
40°	391.1
42.5°	323.3
45°	259.0
47.5°	201.7
50°	153.0
52.5°	113.0
55°	81.7
57.5°	57.4
60°	41.7
62.5°	31.3
65°	22.6
67.5°	17.4
70°	12.2
72.5°	8.7
75°	7.0
77.5°	3.5
80°	3.5
82.5°	1.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)