

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205698

Luminaire Tested: **LD4B15D010 EU4B10209035 4LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205698
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10209035 4LBSH1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1272.0 lumens
Efficiency: N/A
Efficacy: 89.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205698

CATALOG NUMBER: LD4B15D010 EU4B10209035 4LB5H1

Luminous Intensity Polar Plot





TEST NUMBER: P205698

CATALOG NUMBER: LD4B15D010 EU4B10209035 4LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205698

CATALOG NUMBER: LD4B15D010 EU4B10209035 4LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.3	4.9
10°-20°	169.4	13.3
20°-30°	235.2	18.5
30°-40°	256.7	20.2
40°-50°	239.4	18.8
50°-60°	181.8	14.3
60°-70°	99.5	7.8
70°-80°	27.4	2.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	466.9	36.7
0°-40°	723.6	56.9
0°-60°	1144.8	90.0
0°-90°	1272.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1272.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	665	
5°	660	62
15°	604	169
25°	511	235
35°	410	257
45°	311	239
55°	203	182
65°	99	100
75°	24	27
85°	0	0
90°	0	



TEST NUMBER: P205698

CATALOG NUMBER: LD4B15D010 EU4B10209035 4LBSH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	665.3
2.5°	665.3
5°	659.7
7.5°	651.3
10°	638.7
12.5°	621.9
15°	603.6
17.5°	581.2
20°	560.2
22.5°	535.0
25°	511.2
27.5°	487.4
30°	460.8
32.5°	435.6
35°	410.4
37.5°	385.2
40°	361.3
42.5°	336.1
45°	310.9
47.5°	285.7
50°	257.7
52.5°	231.1
55°	203.1
57.5°	176.5
60°	149.9
62.5°	123.3
65°	99.4
67.5°	77.0
70°	57.4
72.5°	39.2
75°	23.8
77.5°	11.2
80°	2.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)