

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206420

Luminaire Tested: **LD4B15D010 EU4B10208040 4LBCSMB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206420  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B15D010 EU4B10208040 4LBCSMB1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM  
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W  
DL3-15.28W DLE-15.432W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1513.4 lumens  
Efficiency: N/A  
Efficacy: 105.8 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206420

CATALOG NUMBER: LD4B15D010 EU4B10208040 4LBCSMB1

### Luminous Intensity Polar Plot





TEST NUMBER: P206420

CATALOG NUMBER: LD4B15D010 EU4B10208040 4LBCSMB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88	88	88	88
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75	75	75	75
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65	65	65	65
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56	56	56	56
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49	49	49	49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43	43	43	43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39	39	39	39
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35	35	35	35
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31	31	31	31
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28	28	28	28

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206420

CATALOG NUMBER: LD4B15D010 EU4B10208040 4LBCSMB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	60.4	4.0
10°-20°	172.2	11.4
20°-30°	258.9	17.1
30°-40°	307.2	20.3
40°-50°	304.0	20.1
50°-60°	238.8	15.8
60°-70°	133.9	8.8
70°-80°	37.6	2.5
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	491.5	32.5
0°-40°	798.7	52.8
0°-60°	1341.4	88.6
0°-90°	1513.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1513.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	639	
5°	638	60
15°	611	172
25°	562	259
35°	493	307
45°	396	304
55°	269	239
65°	134	134
75°	32	38
85°	0	1
90°	0	



TEST NUMBER: P206420

CATALOG NUMBER: LD4B15D010 EU4B10208040 4LBCSMB1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	639.0
2.5°	636.9
5°	638.0
7.5°	632.5
10°	626.0
12.5°	618.4
15°	610.8
17.5°	601.1
20°	588.1
22.5°	575.0
25°	562.0
27.5°	547.9
30°	529.5
32.5°	511.0
35°	492.6
37.5°	470.9
40°	445.9
42.5°	422.1
45°	396.0
47.5°	366.7
50°	336.3
52.5°	301.6
55°	269.1
57.5°	232.2
60°	197.5
62.5°	166.0
65°	133.5
67.5°	105.2
70°	78.1
72.5°	53.2
75°	32.5
77.5°	16.3
80°	4.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)