

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P755948

Luminaire Tested: LD4D90BD010-EU4DR6570959050-4LBSQW1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P755948  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D90BD010-EU4DR6570959050-4LBSQW1MW  
Description: 4 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7218.2 lumens  
Efficiency: N/A  
Efficacy: 73.0 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 98.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P755948  
CATALOG NUMBER: LD4D90BD010-EU4DR6570959050-4LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P755948

CATALOG NUMBER: LD4D90BD010-EU4DR6570959050-4LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	776494
5°	777135
10°	804494
15°	805820
20°	741902
25°	632135
30°	483925
35°	341887
40°	201807
45°	81925
50°	29695
55°	16554
60°	9484
65°	5222
70°	5495
75°	4264
80°	4467
85°	3761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 81925 cd/sqm



TEST NUMBER: P755948

CATALOG NUMBER: LD4D90BD010-EU4DR6570959050-4LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	684.3	9.5
10°-20°	1974.0	27.3
20°-30°	2368.4	32.8
30°-40°	1591.6	22.1
40°-50°	476.5	6.6
50°-60°	84.1	1.2
60°-70°	23.9	0.3
70°-80°	11.7	0.2
80°-90°	3.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5026.7	69.6
0°-40°	6618.3	91.7
0°-60°	7178.9	99.5
0°-90°	7218.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7218.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7107	
5°	7086	684
15°	7124	1974
25°	5244	2368
35°	2563	1592
45°	530	476
55°	87	84
65°	20	24
75°	10	12
85°	3	4
90°	0	



TEST NUMBER: P755948

CATALOG NUMBER: LD4D90BD010-EU4DR6570959050-4LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7106.8
2.5°	7137.1
5°	7085.6
7.5°	7192.6
10°	7251.2
12.5°	7237.1
15°	7123.9
17.5°	6847.2
20°	6380.7
22.5°	5831.3
25°	5243.5
27.5°	4580.0
30°	3835.7
32.5°	3161.0
35°	2563.2
37.5°	1972.4
40°	1414.9
42.5°	924.1
45°	530.2
47.5°	280.8
50°	174.7
52.5°	121.2
55°	86.9
57.5°	62.6
60°	43.4
62.5°	28.3
65°	20.2
67.5°	18.2
70°	17.2
72.5°	13.1
75°	10.1
77.5°	9.1
80°	7.1
82.5°	5.0
85°	3.0
87.5°	2.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)