

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206729

Luminaire Tested: **LD4B15D010 EU4B10208040 4LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206729
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10208040 4LBWWH1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1344.0 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206729

CATALOG NUMBER: LD4B15D010 EU4B10208040 4LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P206729

CATALOG NUMBER: LD4B15D010 EU4B10208040 4LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92			92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	87	85	84			84
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	88	79	72	67	86	78	71	67	76	70	66	74	69	65	72	68	65	63			63
6	83	73	66	61	81	72	65	61	70	64	60	69	64	60	67	63	59	58			58
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53			53
8	73	62	56	51	72	62	55	51	61	55	51	60	54	50	59	54	50	49			49
9	69	58	51	47	68	58	51	47	57	51	47	56	50	47	55	50	46	45			45
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41			41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206729

CATALOG NUMBER: LD4B15D010 EU4B10208040 4LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.4	6.1
10°-20°	251.9	18.7
20°-30°	387.4	28.8
30°-40°	373.8	27.8
40°-50°	194.9	14.5
50°-60°	41.0	3.1
60°-70°	9.5	0.7
70°-80°	3.7	0.3
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	720.7	53.6
0°-40°	1094.6	81.4
0°-60°	1330.5	99.0
0°-90°	1344.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1344.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	840	
5°	847	81
15°	891	252
25°	849	387
35°	606	374
45°	248	195
55°	37	41
65°	9	10
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P206729

CATALOG NUMBER: LD4B15D010 EU4B10208040 4LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	840.3
2.5°	842.1
5°	847.3
7.5°	854.4
10°	864.9
12.5°	879.0
15°	891.3
17.5°	898.3
20°	893.0
22.5°	882.5
25°	849.1
27.5°	808.7
30°	755.9
32.5°	685.6
35°	606.5
37.5°	520.4
40°	430.7
42.5°	341.0
45°	247.9
47.5°	167.0
50°	107.2
52.5°	65.0
55°	36.9
57.5°	22.9
60°	15.8
62.5°	12.3
65°	8.8
67.5°	7.0
70°	5.3
72.5°	5.3
75°	3.5
77.5°	1.8
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)