

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205595

Luminaire Tested: **LD4B15D010 EU4B10209040 4LBSWMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205595  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B15D010 EU4B10209040 4LBSWMH1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM  
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W  
DL3-15.28W DLE-15.432W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1292.1 lumens  
Efficiency: N/A  
Efficacy: 90.4 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205595

CATALOG NUMBER: LD4B15D010 EU4B10209040 4LBSWMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P205595

CATALOG NUMBER: LD4B15D010 EU4B10209040 4LBSWMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90																			
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79																			
3	96	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70																			
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62																			
5	83	73	65	59	82	72	64	59	70	63	59	68	62	58	66	61	57	56																			
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50																			
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45																			
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41																			
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38																			
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205595

CATALOG NUMBER: LD4B15D010 EU4B10209040 4LBSWMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	75.7	5.9
10°-20°	200.6	15.5
20°-30°	269.4	20.8
30°-40°	275.7	21.3
40°-50°	238.7	18.5
50°-60°	158.7	12.3
60°-70°	65.2	5.0
70°-80°	7.8	0.6
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	545.6	42.2
0°-40°	821.4	63.6
0°-60°	1218.8	94.3
0°-90°	1292.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1292.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	819	
5°	806	76
15°	716	201
25°	588	269
35°	440	276
45°	311	239
55°	176	159
65°	64	65
75°	3	8
85°	0	0
90°	0	



TEST NUMBER: P205595

CATALOG NUMBER: LD4B15D010 EU4B10209040 4LBSWMH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	818.9
2.5°	817.2
5°	806.2
7.5°	789.3
10°	766.4
12.5°	741.0
15°	716.5
17.5°	685.1
20°	654.6
22.5°	622.5
25°	587.7
27.5°	550.5
30°	513.2
32.5°	475.9
35°	440.4
37.5°	406.5
40°	374.3
42.5°	342.1
45°	310.8
47.5°	277.8
50°	243.9
52.5°	210.0
55°	176.2
57.5°	146.5
60°	116.0
62.5°	88.1
65°	64.4
67.5°	42.3
70°	24.6
72.5°	11.9
75°	3.4
77.5°	1.7
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)