

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206530

Luminaire Tested: **LD4B15D010 EU4B10209050 4LBCSMMS1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206530
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B15D010 EU4B10209050 4LBCSMMS1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1148.5 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206530

CATALOG NUMBER: LD4B15D010 EU4B10209050 4LBCSMMS1

Luminous Intensity Polar Plot





TEST NUMBER: P206530

CATALOG NUMBER: LD4B15D010 EU4B10209050 4LBCSMMS1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76			
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65			
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57			
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50			
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44			
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40			
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36			
9	60	48	40	34	59	47	40	34	46	39	34	45	39	34	44	38	34	32			
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206530

CATALOG NUMBER: LD4B15D010 EU4B10209050 4LBCSMMS1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.7	4.3
10°-20°	139.5	12.1
20°-30°	203.7	17.7
30°-40°	233.0	20.3
40°-50°	223.9	19.5
50°-60°	172.9	15.1
60°-70°	96.5	8.4
70°-80°	28.1	2.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	392.8	34.2
0°-40°	625.8	54.5
0°-60°	1022.6	89.0
0°-90°	1148.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1148.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	527	
5°	523	50
15°	495	139
25°	443	204
35°	373	233
45°	292	224
55°	194	173
65°	97	97
75°	24	28
85°	1	1
90°	0	



TEST NUMBER: P206530

CATALOG NUMBER: LD4B15D010 EU4B10209050 4LBCSMMS1

CANDELA DISTRIBUTION (FULL):

	0°
0°	527.4
2.5°	527.4
5°	522.9
7.5°	520.7
10°	513.3
12.5°	504.4
15°	494.7
17.5°	485.0
20°	470.9
22.5°	459.8
25°	442.7
27.5°	425.6
30°	408.5
32.5°	391.5
35°	372.9
37.5°	354.3
40°	332.8
42.5°	313.5
45°	291.9
47.5°	267.4
50°	244.4
52.5°	219.1
55°	193.9
57.5°	167.9
60°	143.4
62.5°	118.8
65°	96.6
67.5°	75.8
70°	56.5
72.5°	39.4
75°	24.5
77.5°	12.6
80°	4.5
82.5°	1.5
85°	0.7
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)