

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207354

Luminaire Tested: **LD4B15D010 EU4B10209050 4LBMGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P207354  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B15D010 EU4B10209050 4LBMGPH1  
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W  
DL3-15.28W DLE-15.432W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 703.3 lumens  
Efficiency: N/A  
Efficacy: 49.2 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.92  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P207354

CATALOG NUMBER: LD4B15D010 EU4B10209050 4LBMGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P207354

CATALOG NUMBER: LD4B15D010 EU4B10209050 4LBMGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93																											
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	88	86																											
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79																											
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73																											
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68																											
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63																											
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59																											
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55																											
9	73	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	52	51																											
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	52	49	48																											

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P207354

CATALOG NUMBER: LD4B15D010 EU4B10209050 4LBMGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	66.5	9.5
10°-20°	173.5	24.7
20°-30°	222.5	31.6
30°-40°	160.8	22.9
40°-50°	57.7	8.2
50°-60°	15.6	2.2
60°-70°	5.1	0.7
70°-80°	1.6	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	462.5	65.8
0°-40°	623.4	88.6
0°-60°	696.6	99.0
0°-90°	703.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	703.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	723	
5°	710	67
15°	618	173
25°	491	223
35°	257	161
45°	70	58
55°	16	16
65°	4	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P207354

CATALOG NUMBER: LD4B15D010 EU4B10209050 4LBMGPH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	723.0
2.5°	720.0
5°	709.7
7.5°	693.4
10°	671.2
12.5°	646.1
15°	618.0
17.5°	589.9
20°	561.8
22.5°	529.3
25°	490.9
27.5°	446.5
30°	390.3
32.5°	325.3
35°	257.3
37.5°	195.2
40°	141.9
42.5°	100.5
45°	69.5
47.5°	47.3
50°	31.0
52.5°	22.2
55°	16.3
57.5°	11.8
60°	8.9
62.5°	7.4
65°	4.4
67.5°	3.0
70°	3.0
72.5°	1.5
75°	1.5
77.5°	1.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)