

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208074

Luminaire Tested: **LD4B15D010 EU4B10209050 4LBWLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P208074  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B15D010 EU4B10209050 4LBWLI1  
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W  
DL3-15.28W DLE-15.432W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1289.8 lumens  
Efficiency: N/A  
Efficacy: 90.2 lumens/watt  
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P208074

CATALOG NUMBER: LD4B15D010 EU4B10209050 4LBWLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P208074

CATALOG NUMBER: LD4B15D010 EU4B10209050 4LBWLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			92																
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			84																
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77			77																
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70			70																
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64			64																
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58			58																
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54			54																
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49			49																
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45			45																
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42			42																

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P208074

CATALOG NUMBER: LD4B15D010 EU4B10209050 4LBWLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	77.3	6.0
10°-20°	243.9	18.9
20°-30°	380.5	29.5
30°-40°	370.2	28.7
40°-50°	184.9	14.3
50°-60°	28.6	2.2
60°-70°	3.5	0.3
70°-80°	1.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	701.6	54.4
0°-40°	1071.8	83.1
0°-60°	1285.3	99.7
0°-90°	1289.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1289.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	790	
5°	801	77
15°	861	244
25°	836	380
35°	601	370
45°	232	185
55°	24	29
65°	3	3
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P208074

CATALOG NUMBER: LD4B15D010 EU4B10209050 4LBWLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	790.3
2.5°	793.2
5°	800.6
7.5°	812.4
10°	827.2
12.5°	846.4
15°	861.2
17.5°	873.0
20°	874.5
22.5°	864.1
25°	836.1
27.5°	794.7
30°	743.0
32.5°	678.0
35°	601.2
37.5°	517.0
40°	428.4
42.5°	333.8
45°	231.9
47.5°	149.2
50°	90.1
52.5°	48.7
55°	23.6
57.5°	10.3
60°	5.9
62.5°	4.4
65°	3.0
67.5°	3.0
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)