

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207570

Luminaire Tested: **LD4B20D010 EU4B10209030 4LBMMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P207570  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B20D010 EU4B10209030 4LBMMW1  
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1353.8 lumens  
Efficiency: N/A  
Efficacy: 65.1 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P207570

CATALOG NUMBER: LD4B20D010 EU4B10209030 4LBMMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P207570

CATALOG NUMBER: LD4B20D010 EU4B10209030 4LBMMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89				89
2	104	98	92	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80				80
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71				71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	69	66	64				64
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58				58
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53				53
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49				49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45				45
9	67	55	48	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42				42
10	63	52	45	41	62	51	45	41	51	45	40	50	44	40	49	44	40	39				39

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P207570

CATALOG NUMBER: LD4B20D010 EU4B10209030 4LBMMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	95.3	7.0
10°-20°	255.4	18.9
20°-30°	339.6	25.1
30°-40°	277.7	20.5
40°-50°	161.8	11.9
50°-60°	107.3	7.9
60°-70°	70.6	5.2
70°-80°	37.2	2.7
80°-90°	9.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	690.2	51.0
0°-40°	967.9	71.5
0°-60°	1236.9	91.4
0°-90°	1353.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1353.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1028	
5°	1016	95
15°	910	255
25°	745	340
35°	443	278
45°	204	162
55°	120	107
65°	71	71
75°	35	37
85°	8	9
90°	0	



TEST NUMBER: P207570

CATALOG NUMBER: LD4B20D010 EU4B10209030 4LBMMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1027.7
2.5°	1025.7
5°	1015.9
7.5°	992.4
10°	966.9
12.5°	943.4
15°	910.0
17.5°	872.8
20°	841.4
22.5°	798.2
25°	745.3
27.5°	688.4
30°	615.8
32.5°	529.5
35°	443.2
37.5°	364.8
40°	296.2
42.5°	243.2
45°	204.0
47.5°	172.6
50°	151.0
52.5°	133.4
55°	119.6
57.5°	105.9
60°	92.2
62.5°	82.4
65°	70.6
67.5°	60.8
70°	51.0
72.5°	43.1
75°	35.3
77.5°	27.5
80°	19.6
82.5°	13.7
85°	7.8
87.5°	2.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)