

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756328

Luminaire Tested: LD4D95BD010-EU4DR4070959050-4LBCSSQMW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756328
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR4070959050-4LBCSSQMW
Description: 4 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9269.2 lumens
Efficiency: N/A
Efficacy: 93.4 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P756328
CATALOG NUMBER: LD4D95BD010-EU4DR4070959050-4LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P756328

CATALOG NUMBER: LD4D95BD010-EU4DR4070959050-4LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																		
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96									96																		
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92									92																		
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88									88																		
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84									84																		
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81									81																		
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77									77																		
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74									74																		
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72									72																		
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69									69																		
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67									67																		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2357978
5°	2346519
10°	2217971
15°	1885560
20°	1285141
25°	536221
30°	168605
35°	78362
40°	43331
45°	19871
50°	9638
55°	5277
60°	2753
65°	982
70°	415
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19871 cd/sqm



TEST NUMBER: P756328

CATALOG NUMBER: LD4D95BD010-EU4DR4070959050-4LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1997.7	21.6
10°-20°	4475.4	48.3
20°-30°	2240.3	24.2
30°-40°	410.7	4.4
40°-50°	113.3	1.2
50°-60°	26.6	0.3
60°-70°	5.1	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8713.4	94.0
0°-40°	9124.0	98.4
0°-60°	9263.9	99.9
0°-90°	9269.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9269.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	21581	
5°	21395	###
15°	16669	4475
25°	4448	2240
35°	588	411
45°	129	113
55°	28	27
65°	4	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756328

CATALOG NUMBER: LD4D95BD010-EU4DR4070959050-4LBCSSQMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	21581.2
2.5°	21549.7
5°	21394.6
7.5°	20900.4
10°	19991.4
12.5°	18574.3
15°	16669.4
17.5°	14192.0
20°	11052.8
22.5°	7535.4
25°	4447.9
27.5°	2351.3
30°	1336.4
32.5°	863.6
35°	587.5
37.5°	419.8
40°	303.8
42.5°	208.0
45°	128.6
47.5°	81.9
50°	56.7
52.5°	40.3
55°	27.7
57.5°	17.7
60°	12.6
62.5°	7.6
65°	3.8
67.5°	2.5
70°	1.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)