

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207261

Luminaire Tested: **LD4B20D010 EU4B10209030 4LBMWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P207261  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B20D010 EU4B10209030 4LBMWH1  
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1328.3 lumens  
Efficiency: N/A  
Efficacy: 63.9 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.87  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P207261

CATALOG NUMBER: LD4B20D010 EU4B10209030 4LBMWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P207261

CATALOG NUMBER: LD4B20D010 EU4B10209030 4LBMWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	105	105	103	101	101	100	98	98	96	95	94		
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87		
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81		
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76		
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71		
6	88	79	73	69	87	79	73	69	77	72	68	76	71	68	74	71	68	66		
7	84	75	69	65	82	74	68	64	73	68	64	72	67	64	70	66	63	62		
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58		
9	76	66	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55		
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P207261

CATALOG NUMBER: LD4B20D010 EU4B10209030 4LBMWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	145.7	11.0
10°-20°	374.7	28.2
20°-30°	439.6	33.1
30°-40°	278.2	20.9
40°-50°	74.5	5.6
50°-60°	10.4	0.8
60°-70°	3.9	0.3
70°-80°	1.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	960.0	72.3
0°-40°	1238.2	93.2
0°-60°	1323.1	99.6
0°-90°	1328.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1328.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1578	
5°	1552	146
15°	1342	375
25°	971	440
35°	442	278
45°	84	75
55°	10	10
65°	4	4
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P207261

CATALOG NUMBER: LD4B20D010 EU4B10209030 4LBMWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1577.5
2.5°	1571.6
5°	1552.0
7.5°	1520.6
10°	1475.5
12.5°	1416.6
15°	1342.1
17.5°	1265.6
20°	1173.3
22.5°	1079.2
25°	971.2
27.5°	853.5
30°	722.1
32.5°	578.8
35°	441.5
37.5°	319.8
40°	219.8
42.5°	141.3
45°	84.4
47.5°	47.1
50°	25.5
52.5°	13.7
55°	9.8
57.5°	7.8
60°	5.9
62.5°	5.9
65°	3.9
67.5°	2.0
70°	2.0
72.5°	2.0
75°	2.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)