

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206507

Luminaire Tested: **LD4B10D010 EU4B10208027 4LBCSMMS1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206507
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10208027 4LBCSMMS1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 905.6 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206507

CATALOG NUMBER: LD4B10D010 EU4B10208027 4LBCSMMS1

Luminous Intensity Polar Plot





TEST NUMBER: P206507

CATALOG NUMBER: LD4B10D010 EU4B10208027 4LBCSMMS1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88				88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	83	80	78	76				76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65				65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57				57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50				50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44				44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40				40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36				36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32				32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29				29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206507

CATALOG NUMBER: LD4B10D010 EU4B10208027 4LBCSMMS1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.2	4.3
10°-20°	110.0	12.1
20°-30°	160.6	17.7
30°-40°	183.7	20.3
40°-50°	176.6	19.5
50°-60°	136.3	15.1
60°-70°	76.1	8.4
70°-80°	22.1	2.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	309.8	34.2
0°-40°	493.5	54.5
0°-60°	806.4	89.0
0°-90°	905.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	905.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	416	
5°	412	39
15°	390	110
25°	349	161
35°	294	184
45°	230	177
55°	153	136
65°	76	76
75°	19	22
85°	1	1
90°	0	



TEST NUMBER: P206507

CATALOG NUMBER: LD4B10D010 EU4B10208027 4LBCSMMS1

CANDELA DISTRIBUTION (FULL):

	0°
0°	415.9
2.5°	415.9
5°	412.3
7.5°	410.6
10°	404.7
12.5°	397.7
15°	390.1
17.5°	382.5
20°	371.3
22.5°	362.6
25°	349.1
27.5°	335.6
30°	322.1
32.5°	308.7
35°	294.0
37.5°	279.4
40°	262.4
42.5°	247.2
45°	230.2
47.5°	210.9
50°	192.7
52.5°	172.8
55°	152.9
57.5°	132.4
60°	113.0
62.5°	93.7
65°	76.1
67.5°	59.7
70°	44.5
72.5°	31.0
75°	19.3
77.5°	10.0
80°	3.5
82.5°	1.2
85°	0.6
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)