

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206746

Luminaire Tested: **LD4B20D010 EU4B10209030 4LBWWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206746  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B20D010 EU4B10209030 4LBWWH1  
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1500.9 lumens  
Efficiency: N/A  
Efficacy: 72.2 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206746

CATALOG NUMBER: LD4B20D010 EU4B10209030 4LBWWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P206746

CATALOG NUMBER: LD4B20D010 EU4B10209030 4LBWWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     | 0   |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1   | 113 | 110 | 107 | 104 | 110 | 107 | 105 | 103 | 103 | 101 | 100 | 100 | 98  | 97  | 96  | 95  | 94  | 92  | 92  | 92  | 92  |
| 2   | 106 | 101 | 96  | 92  | 104 | 99  | 95  | 91  | 96  | 92  | 89  | 93  | 90  | 87  | 90  | 87  | 85  | 84  | 84  | 84  | 84  |
| 3   | 100 | 93  | 87  | 82  | 98  | 91  | 86  | 82  | 88  | 84  | 80  | 86  | 82  | 79  | 84  | 80  | 78  | 76  | 76  | 76  | 76  |
| 4   | 94  | 85  | 79  | 74  | 92  | 84  | 78  | 74  | 82  | 77  | 73  | 80  | 75  | 72  | 78  | 74  | 71  | 69  | 69  | 69  | 69  |
| 5   | 88  | 79  | 72  | 67  | 86  | 78  | 71  | 67  | 76  | 70  | 66  | 74  | 69  | 65  | 72  | 68  | 65  | 63  | 63  | 63  | 63  |
| 6   | 83  | 73  | 66  | 61  | 81  | 72  | 65  | 61  | 70  | 64  | 60  | 69  | 64  | 60  | 67  | 63  | 59  | 58  | 58  | 58  | 58  |
| 7   | 78  | 67  | 60  | 56  | 76  | 67  | 60  | 55  | 65  | 59  | 55  | 64  | 59  | 55  | 63  | 58  | 54  | 53  | 53  | 53  | 53  |
| 8   | 73  | 62  | 56  | 51  | 72  | 62  | 55  | 51  | 61  | 55  | 51  | 60  | 54  | 50  | 59  | 54  | 50  | 49  | 49  | 49  | 49  |
| 9   | 69  | 58  | 51  | 47  | 68  | 58  | 51  | 47  | 57  | 51  | 47  | 56  | 50  | 47  | 55  | 50  | 46  | 45  | 45  | 45  | 45  |
| 10  | 65  | 54  | 48  | 43  | 64  | 54  | 48  | 43  | 53  | 47  | 43  | 52  | 47  | 43  | 51  | 46  | 43  | 41  | 41  | 41  | 41  |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206746

CATALOG NUMBER: LD4B20D010 EU4B10209030 4LBWWH1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 90.9   | 6.1       |
| 10°-20°   | 281.3  | 18.7      |
| 20°-30°   | 432.7  | 28.8      |
| 30°-40°   | 417.5  | 27.8      |
| 40°-50°   | 217.7  | 14.5      |
| 50°-60°   | 45.8   | 3.1       |
| 60°-70°   | 10.6   | 0.7       |
| 70°-80°   | 4.1    | 0.3       |
| 80°-90°   | 0.3    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 804.9  | 53.6      |
| 0°-40°    | 1222.4 | 81.4      |
| 0°-60°    | 1485.9 | 99.0      |
| 0°-90°    | 1500.9 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1500.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 938 |      |
| 5°  | 946 | 91   |
| 15° | 995 | 281  |
| 25° | 948 | 433  |
| 35° | 677 | 417  |
| 45° | 277 | 218  |
| 55° | 41  | 46   |
| 65° | 10  | 11   |
| 75° | 4   | 4    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P206746

CATALOG NUMBER: LD4B20D010 EU4B10209030 4LBWWH1

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 938.5  |
| 2.5°  | 940.4  |
| 5°    | 946.3  |
| 7.5°  | 954.2  |
| 10°   | 965.9  |
| 12.5° | 981.7  |
| 15°   | 995.4  |
| 17.5° | 1003.2 |
| 20°   | 997.4  |
| 22.5° | 985.6  |
| 25°   | 948.3  |
| 27.5° | 903.1  |
| 30°   | 844.2  |
| 32.5° | 765.7  |
| 35°   | 677.3  |
| 37.5° | 581.1  |
| 40°   | 481.0  |
| 42.5° | 380.9  |
| 45°   | 276.8  |
| 47.5° | 186.5  |
| 50°   | 119.8  |
| 52.5° | 72.6   |
| 55°   | 41.2   |
| 57.5° | 25.5   |
| 60°   | 17.7   |
| 62.5° | 13.7   |
| 65°   | 9.8    |
| 67.5° | 7.9    |
| 70°   | 5.9    |
| 72.5° | 5.9    |
| 75°   | 3.9    |
| 77.5° | 2.0    |
| 80°   | 2.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)