

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207332

Luminaire Tested: **LD4B10D010 EU4B10208027 4LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207332
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10208027 4LBMGPH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 554.6 lumens
Efficiency: N/A
Efficacy: 56.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.92
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207332

CATALOG NUMBER: LD4B10D010 EU4B10208027 4LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P207332

CATALOG NUMBER: LD4B10D010 EU4B10208027 4LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93																											
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	88	86																											
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79																											
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73																											
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68																											
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63																											
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59																											
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55																											
9	73	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	52	51																											
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	52	49	48																											

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207332

CATALOG NUMBER: LD4B10D010 EU4B10208027 4LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.5	9.5
10°-20°	136.8	24.7
20°-30°	175.5	31.6
30°-40°	126.8	22.9
40°-50°	45.5	8.2
50°-60°	12.3	2.2
60°-70°	4.0	0.7
70°-80°	1.3	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	364.7	65.8
0°-40°	491.6	88.6
0°-60°	549.3	99.1
0°-90°	554.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	554.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	570	
5°	560	52
15°	487	137
25°	387	175
35°	203	127
45°	55	45
55°	13	12
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P207332

CATALOG NUMBER: LD4B10D010 EU4B10208027 4LBMGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	570.1
2.5°	567.8
5°	559.6
7.5°	546.8
10°	529.3
12.5°	509.5
15°	487.3
17.5°	465.2
20°	443.0
22.5°	417.4
25°	387.1
27.5°	352.1
30°	307.8
32.5°	256.5
35°	202.9
37.5°	153.9
40°	111.9
42.5°	79.3
45°	54.8
47.5°	37.3
50°	24.5
52.5°	17.5
55°	12.8
57.5°	9.3
60°	7.0
62.5°	5.8
65°	3.5
67.5°	2.3
70°	2.3
72.5°	1.2
75°	1.2
77.5°	1.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)