

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P35290

Luminaire Tested: **LD4B10D010 EU4B10209027 4LBMLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P35290  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B10D010 EU4B10209027 4LBMLI1  
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W  
DL3-11.1W DLE-11.39W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 826.5 lumens  
Efficiency: N/A  
Efficacy: 84.9 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.73  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P35290

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBMLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P35290

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBMLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	142367
5°	139949
10°	128587
15°	107686
20°	86274
25°	69320
30°	51601
35°	29478
40°	13835
45°	5872
50°	1870
55°	952
60°	656
65°	517
70°	319
75°	0
80°	0
85°	0



TEST NUMBER: P35290

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBMLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	118.0	14.3
10°-20°	263.8	31.9
20°-30°	262.2	31.7
30°-40°	142.8	17.3
40°-50°	33.0	4.0
50°-60°	4.6	0.6
60°-70°	1.7	0.2
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	644.0	77.9
0°-40°	786.8	95.2
0°-60°	824.4	99.7
0°-90°	826.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	826.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1303	
5°	1276	118
15°	952	264
25°	575	262
35°	221	143
45°	38	33
55°	5	5
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P35290

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBMLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1303
2.5°	1300
5°	1276
7.5°	1227
10°	1159
12.5°	1059
15°	952
17.5°	846
20°	742
22.5°	657
25°	575
27.5°	497
30°	409
32.5°	311
35°	221
37.5°	149
40°	97
42.5°	61
45°	38
47.5°	22
50°	11
52.5°	6
55°	5
57.5°	3
60°	3
62.5°	2
65°	2
67.5°	1
70°	1
72.5°	1
75°	0
77.5°	0
80°	0
82.5°	0
85°	0
87.5°	0
90°	0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)