

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207060

Luminaire Tested: **LD4B20D010 EU4B10209730 4LBWMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P207060  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B20D010 EU4B10209730 4LBWMW1  
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W  
DL3-21.8 6W DLE-22.46W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1320.2 lumens  
Efficiency: N/A  
Efficacy: 63.5 lumens/watt  
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P207060

CATALOG NUMBER: LD4B20D010 EU4B10209730 4LBWMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P207060

CATALOG NUMBER: LD4B20D010 EU4B10209730 4LBWMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78		
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69		
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61		
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55		
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	60	55	51	50		
7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45		
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	61	49	42	37	59	48	41	37	47	41	37	46	41	37	46	40	36	35		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P207060

CATALOG NUMBER: LD4B20D010 EU4B10209730 4LBWMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	75.1	5.7
10°-20°	210.1	15.9
20°-30°	296.9	22.5
30°-40°	287.6	21.8
40°-50°	194.0	14.7
50°-60°	120.4	9.1
60°-70°	80.5	6.1
70°-80°	44.0	3.3
80°-90°	11.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	582.0	44.1
0°-40°	869.6	65.9
0°-60°	1184.1	89.7
0°-90°	1320.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1320.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	800	
5°	793	75
15°	745	210
25°	651	297
35°	463	288
45°	248	194
55°	132	120
65°	80	80
75°	41	44
85°	10	12
90°	0	



TEST NUMBER: P207060

CATALOG NUMBER: LD4B20D010 EU4B10209730 4LBMMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	800.0
2.5°	800.0
5°	793.2
7.5°	784.6
10°	774.3
12.5°	764.1
15°	745.2
17.5°	729.8
20°	704.1
22.5°	678.4
25°	651.0
27.5°	613.3
30°	572.2
32.5°	519.1
35°	462.6
37.5°	406.0
40°	349.5
42.5°	292.9
45°	248.4
47.5°	207.3
50°	176.5
52.5°	150.8
55°	131.9
57.5°	116.5
60°	104.5
62.5°	92.5
65°	80.5
67.5°	70.2
70°	60.0
72.5°	51.4
75°	41.1
77.5°	32.5
80°	24.0
82.5°	17.1
85°	10.3
87.5°	3.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)