

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P35206

Luminaire Tested: **LD4B10D010 EU4B10209027 4LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P35206
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10209027 4LBNGPH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 412.8 lumens
Efficiency: N/A
Efficacy: 42.4 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.88
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 9.73
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P35206

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P35206

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	68	63	60	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	54084
5°	52975
10°	49704
15°	45698
20°	41044
25°	36408
30°	30027
35°	19340
40°	9271
45°	3554
50°	1190
55°	762
60°	656
65°	259
70°	319
75°	0
80°	0
85°	0



TEST NUMBER: P35206

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.0	10.9
10°-20°	112.8	27.3
20°-30°	137.5	33.3
30°-40°	90.7	22.0
40°-50°	20.9	5.1
50°-60°	4.0	1.0
60°-70°	1.5	0.4
70°-80°	0.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	295.3	71.5
0°-40°	386.0	93.5
0°-60°	410.9	99.5
0°-90°	412.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	412.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	495	
5°	483	45
15°	404	113
25°	302	137
35°	145	91
45°	23	21
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P35206

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBNGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	495
2.5°	494
5°	483
7.5°	468
10°	448
12.5°	428
15°	404
17.5°	379
20°	353
22.5°	330
25°	302
27.5°	274
30°	238
32.5°	194
35°	145
37.5°	101
40°	65
42.5°	40
45°	23
47.5°	12
50°	7
52.5°	6
55°	4
57.5°	3
60°	3
62.5°	2
65°	1
67.5°	1
70°	1
72.5°	1
75°	0
77.5°	0
80°	0
82.5°	0
85°	0
87.5°	0
90°	0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)