

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205683

Luminaire Tested: **LD4B10D010 EU4B10209027 4LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205683
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10209027 4LBSH1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 865.8 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205683

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LB5H1

Luminous Intensity Polar Plot





TEST NUMBER: P205683

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205683

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.4	4.9
10°-20°	115.3	13.3
20°-30°	160.1	18.5
30°-40°	174.7	20.2
40°-50°	163.0	18.8
50°-60°	123.7	14.3
60°-70°	67.7	7.8
70°-80°	18.6	2.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	317.8	36.7
0°-40°	492.5	56.9
0°-60°	779.2	90.0
0°-90°	865.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	865.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	453	
5°	449	42
15°	411	115
25°	348	160
35°	279	175
45°	212	163
55°	138	124
65°	68	68
75°	16	19
85°	0	0
90°	0	



TEST NUMBER: P205683

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBSH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	452.8
2.5°	452.8
5°	449.0
7.5°	443.3
10°	434.7
12.5°	423.3
15°	410.9
17.5°	395.6
20°	381.3
22.5°	364.2
25°	348.0
27.5°	331.8
30°	313.7
32.5°	296.5
35°	279.3
37.5°	262.2
40°	246.0
42.5°	228.8
45°	211.6
47.5°	194.5
50°	175.4
52.5°	157.3
55°	138.2
57.5°	120.1
60°	102.0
62.5°	83.9
65°	67.7
67.5°	52.4
70°	39.1
72.5°	26.7
75°	16.2
77.5°	7.6
80°	1.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)