

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206099

Luminaire Tested: **LD4B10D010 EU4B10209027 4LBSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206099  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B10D010 EU4B10209027 4LBSMW1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W  
DL3-11.1W DLE-11.39W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 903.0 lumens  
Efficiency: N/A  
Efficacy: 91.2 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206099

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P206099

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63			
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206099

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	34.5	3.8
10°-20°	98.3	10.9
20°-30°	148.0	16.4
30°-40°	176.1	19.5
40°-50°	175.8	19.5
50°-60°	142.9	15.8
60°-70°	87.9	9.7
70°-80°	34.0	3.8
80°-90°	5.5	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	280.7	31.1
0°-40°	456.8	50.6
0°-60°	775.5	85.9
0°-90°	903.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	903.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	364	
5°	363	34
15°	349	98
25°	322	148
35°	282	176
45°	228	176
55°	160	143
65°	88	88
75°	31	34
85°	4	5
90°	0	



TEST NUMBER: P206099

CATALOG NUMBER: LD4B10D010 EU4B10209027 4LBSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	363.8
2.5°	364.4
5°	362.8
7.5°	360.6
10°	357.9
12.5°	353.1
15°	348.8
17.5°	342.4
20°	335.5
22.5°	329.0
25°	322.1
27.5°	312.5
30°	302.8
32.5°	293.7
35°	282.0
37.5°	269.1
40°	257.4
42.5°	242.9
45°	228.5
47.5°	212.9
50°	196.4
52.5°	179.2
55°	160.0
57.5°	141.2
60°	123.1
62.5°	105.4
65°	88.3
67.5°	72.2
70°	57.2
72.5°	43.3
75°	31.0
77.5°	20.3
80°	12.3
82.5°	7.5
85°	4.3
87.5°	2.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)