

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P208196

Luminaire Tested: **LD4B30D010 EU4B30509024 4LBMLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P208196
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30509024 4LBMLI1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1978.0 lumens
Efficiency: N/A
Efficacy: 70.6 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P208196

CATALOG NUMBER: LD4B30D010 EU4B30509024 4LBMLI1

Luminous Intensity Polar Plot





TEST NUMBER: P208196

CATALOG NUMBER: LD4B30D010 EU4B30509024 4LBMLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P208196

CATALOG NUMBER: LD4B30D010 EU4B30509024 4LBMLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	282.3	14.3
10°-20°	631.2	31.9
20°-30°	627.6	31.7
30°-40°	341.8	17.3
40°-50°	79.0	4.0
50°-60°	11.1	0.6
60°-70°	4.1	0.2
70°-80°	0.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1541.1	77.9
0°-40°	1882.8	95.2
0°-60°	1973.0	99.7
0°-90°	1978.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1978.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3118	
5°	3054	282
15°	2278	631
25°	1376	628
35°	529	342
45°	91	79
55°	12	11
65°	5	4
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P208196

CATALOG NUMBER: LD4B30D010 EU4B30509024 4LBMLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3118.3
2.5°	3111.1
5°	3053.6
7.5°	2936.4
10°	2773.6
12.5°	2534.3
15°	2278.3
17.5°	2024.6
20°	1775.7
22.5°	1572.3
25°	1376.1
27.5°	1189.4
30°	978.8
32.5°	744.3
35°	528.9
37.5°	356.6
40°	232.1
42.5°	146.0
45°	90.9
47.5°	52.6
50°	26.3
52.5°	14.4
55°	12.0
57.5°	7.2
60°	7.2
62.5°	4.8
65°	4.8
67.5°	2.4
70°	2.4
72.5°	2.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)