

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206208

Luminaire Tested: **LD4B10D010 EU4B10209727 4LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P206208
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10209727 4LBPSMW1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 817.5 lumens
Efficiency: N/A
Efficacy: 82.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P206208

CATALOG NUMBER: LD4B10D010 EU4B10209727 4LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P206208

CATALOG NUMBER: LD4B10D010 EU4B10209727 4LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																			
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P206208

CATALOG NUMBER: LD4B10D010 EU4B10209727 4LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.2	3.8
10°-20°	89.0	10.9
20°-30°	134.0	16.4
30°-40°	159.4	19.5
40°-50°	159.1	19.5
50°-60°	129.4	15.8
60°-70°	79.6	9.7
70°-80°	30.8	3.8
80°-90°	4.9	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	254.1	31.1
0°-40°	413.6	50.6
0°-60°	702.1	85.9
0°-90°	817.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	817.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	329	
5°	328	31
15°	316	89
25°	292	134
35°	255	159
45°	207	159
55°	145	129
65°	80	80
75°	28	31
85°	4	5
90°	0	



TEST NUMBER: P206208

CATALOG NUMBER: LD4B10D010 EU4B10209727 4LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	329.4
2.5°	329.9
5°	328.4
7.5°	326.5
10°	324.0
12.5°	319.7
15°	315.8
17.5°	310.0
20°	303.7
22.5°	297.9
25°	291.6
27.5°	282.9
30°	274.1
32.5°	265.9
35°	255.3
37.5°	243.6
40°	233.0
42.5°	219.9
45°	206.8
47.5°	192.8
50°	177.8
52.5°	162.3
55°	144.8
57.5°	127.9
60°	111.4
62.5°	95.4
65°	79.9
67.5°	65.4
70°	51.8
72.5°	39.2
75°	28.1
77.5°	18.4
80°	11.1
82.5°	6.8
85°	3.9
87.5°	1.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)