

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205617

Luminaire Tested: **LD4B30D010 EU4B30509024 4LBSWMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205617  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B30D010 EU4B30509024 4LBSWMH1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2099.7 lumens  
Efficiency: N/A  
Efficacy: 75.0 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205617

CATALOG NUMBER: LD4B30D010 EU4B30509024 4LBSWMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P205617

CATALOG NUMBER: LD4B30D010 EU4B30509024 4LBSWMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90			
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79			
3	96	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70			
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62			
5	83	73	65	59	82	72	64	59	70	63	59	68	62	58	66	61	57	56			
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50			
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45			
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41			
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38			
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205617

CATALOG NUMBER: LD4B30D010 EU4B30509024 4LBSWMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	123.0	5.9
10°-20°	325.9	15.5
20°-30°	437.7	20.8
30°-40°	448.1	21.3
40°-50°	387.9	18.5
50°-60°	258.0	12.3
60°-70°	105.9	5.0
70°-80°	12.6	0.6
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	886.7	42.2
0°-40°	1334.8	63.6
0°-60°	1980.6	94.3
0°-90°	2099.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2099.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1331	
5°	1310	123
15°	1164	326
25°	955	438
35°	716	448
45°	505	388
55°	286	258
65°	105	106
75°	6	13
85°	0	1
90°	0	



TEST NUMBER: P205617

CATALOG NUMBER: LD4B30D010 EU4B30509024 4LBSWMH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1330.8
2.5°	1328.0
5°	1310.1
7.5°	1282.6
10°	1245.4
12.5°	1204.2
15°	1164.2
17.5°	1113.3
20°	1063.8
22.5°	1011.5
25°	955.1
27.5°	894.5
30°	834.0
32.5°	773.4
35°	715.6
37.5°	660.6
40°	608.3
42.5°	556.0
45°	505.1
47.5°	451.4
50°	396.3
52.5°	341.3
55°	286.2
57.5°	238.1
60°	188.5
62.5°	143.1
65°	104.6
67.5°	68.8
70°	39.9
72.5°	19.3
75°	5.5
77.5°	2.8
80°	1.4
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)