

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206546

Luminaire Tested: **LD4B30D010 EU4B30508027 4LBCSMMS1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206546  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B30D010 EU4B30508027 4LBCSMMS1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2461.2 lumens  
Efficiency: N/A  
Efficacy: 87.9 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206546

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBCSMMS1

### Luminous Intensity Polar Plot





TEST NUMBER: P206546

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBCSMMS1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88				88
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76				76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65				65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57				57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50				50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44				44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40				40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36				36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32				32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29				29

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206546

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBCSMMS1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.5	4.3
10°-20°	298.9	12.1
20°-30°	436.5	17.7
30°-40°	499.3	20.3
40°-50°	479.9	19.5
50°-60°	370.5	15.1
60°-70°	206.8	8.4
70°-80°	60.2	2.4
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	841.9	34.2
0°-40°	1341.2	54.5
0°-60°	2191.6	89.0
0°-90°	2461.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2461.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1130	
5°	1121	107
15°	1060	299
25°	949	437
35°	799	499
45°	626	480
55°	416	371
65°	207	207
75°	52	60
85°	2	3
90°	0	



TEST NUMBER: P206546

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBCSMMS1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1130.2
2.5°	1130.2
5°	1120.7
7.5°	1115.9
10°	1100.0
12.5°	1080.9
15°	1060.2
17.5°	1039.5
20°	1009.2
22.5°	985.4
25°	948.7
27.5°	912.1
30°	875.5
32.5°	838.9
35°	799.1
37.5°	759.3
40°	713.2
42.5°	671.8
45°	625.6
47.5°	573.1
50°	523.7
52.5°	469.6
55°	415.5
57.5°	359.8
60°	307.2
62.5°	254.7
65°	206.9
67.5°	162.4
70°	121.0
72.5°	84.4
75°	52.5
77.5°	27.1
80°	9.6
82.5°	3.2
85°	1.6
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)