

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207576

Luminaire Tested: **LD4B30D010 EU4B30508027 4LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207576
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30508027 4LBMMW1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2184.7 lumens
Efficiency: N/A
Efficacy: 78.0 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207576

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P207576

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89	89	89	89
2	104	98	92	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80	80	80	80
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71	71	71	71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	69	66	64	64	64	64
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58	58	58	58
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53	53	53	53
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49	49	49	49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45	45	45	45
9	67	55	48	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42	42	42	42
10	63	52	45	41	62	51	45	41	51	45	40	50	44	40	49	44	40	39	39	39	39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207576

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.7	7.0
10°-20°	412.1	18.9
20°-30°	548.0	25.1
30°-40°	448.2	20.5
40°-50°	261.1	11.9
50°-60°	173.1	7.9
60°-70°	113.8	5.2
70°-80°	60.1	2.7
80°-90°	14.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1113.8	51.0
0°-40°	1562.0	71.5
0°-60°	1996.2	91.4
0°-90°	2184.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2184.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1658	
5°	1640	154
15°	1469	412
25°	1203	548
35°	715	448
45°	329	261
55°	193	173
65°	114	114
75°	57	60
85°	13	15
90°	0	



TEST NUMBER: P207576

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBMMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1658.5
2.5°	1655.3
5°	1639.5
7.5°	1601.5
10°	1560.3
12.5°	1522.4
15°	1468.6
17.5°	1408.4
20°	1357.8
22.5°	1288.2
25°	1202.7
27.5°	1110.9
30°	993.8
32.5°	854.5
35°	715.3
37.5°	588.7
40°	477.9
42.5°	392.5
45°	329.2
47.5°	278.5
50°	243.7
52.5°	215.2
55°	193.1
57.5°	170.9
60°	148.8
62.5°	132.9
65°	113.9
67.5°	98.1
70°	82.3
72.5°	69.6
75°	57.0
77.5°	44.3
80°	31.6
82.5°	22.2
85°	12.7
87.5°	3.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)