

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205924

Luminaire Tested: **LD4B30D010 EU4B30508027 4LBSGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205924  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B30D010 EU4B30508027 4LBSGPH1  
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2515.3 lumens  
Efficiency: N/A  
Efficacy: 89.8 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205924

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBSGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P205924

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBSGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88	88	88	88
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76	76	76	76
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66	66	66	66
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57	57	57	57
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50	50	50	50
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45	45	45	45
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40	40	40	40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36	36	36	36
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32	32	32	32
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30	30	30	30

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205924

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBSGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	110.0	4.4
10°-20°	308.8	12.3
20°-30°	450.3	17.9
30°-40°	513.5	20.4
40°-50°	492.6	19.6
50°-60°	377.3	15.0
60°-70°	207.0	8.2
70°-80°	55.0	2.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	869.1	34.6
0°-40°	1382.6	55.0
0°-60°	2252.5	89.5
0°-90°	2515.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2515.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1168	
5°	1159	110
15°	1096	309
25°	978	450
35°	821	514
45°	640	493
55°	423	377
65°	208	207
75°	48	55
85°	0	1
90°	0	



TEST NUMBER: P205924

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBSGPH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1168.2
2.5°	1165.2
5°	1159.2
7.5°	1150.1
10°	1138.1
12.5°	1116.9
15°	1095.8
17.5°	1071.6
20°	1044.5
22.5°	1011.3
25°	978.1
27.5°	944.9
30°	902.6
32.5°	863.4
35°	821.1
37.5°	778.8
40°	736.6
42.5°	691.3
45°	640.0
47.5°	588.6
50°	534.3
52.5°	477.0
55°	422.6
57.5°	368.3
60°	310.9
62.5°	256.6
65°	208.3
67.5°	160.0
70°	117.7
72.5°	78.5
75°	48.3
77.5°	21.1
80°	6.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)