

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P206612

Luminaire Tested: **LD4B10D010 EU4B10208030 4LBWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P206612  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B10D010 EU4B10208030 4LBWH1  
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W  
DL3-11.1W DLE-11.39W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 897.5 lumens  
Efficiency: N/A  
Efficacy: 90.7 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P206612

CATALOG NUMBER: LD4B10D010 EU4B10208030 4LBWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P206612

CATALOG NUMBER: LD4B10D010 EU4B10208030 4LBWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82		
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67		
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61		
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55		
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50		
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46		
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43		
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P206612

CATALOG NUMBER: LD4B10D010 EU4B10208030 4LBWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.1	6.1
10°-20°	158.8	17.7
20°-30°	234.3	26.1
30°-40°	231.2	25.8
40°-50°	141.5	15.8
50°-60°	54.2	6.0
60°-70°	16.9	1.9
70°-80°	5.0	0.6
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	448.1	49.9
0°-40°	679.3	75.7
0°-60°	875.0	97.5
0°-90°	897.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	897.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	578	
5°	578	55
15°	563	159
25°	513	234
35°	375	231
45°	182	141
55°	57	54
65°	16	17
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P206612

CATALOG NUMBER: LD4B10D010 EU4B10208030 4LBWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	578.5
2.5°	579.7
5°	578.5
7.5°	577.3
10°	573.7
12.5°	568.8
15°	562.7
17.5°	555.4
20°	544.4
22.5°	532.2
25°	512.8
27.5°	488.4
30°	457.9
32.5°	420.2
35°	375.1
37.5°	325.2
40°	274.0
42.5°	226.5
45°	181.5
47.5°	141.3
50°	107.2
52.5°	79.2
55°	57.2
57.5°	40.2
60°	29.2
62.5°	21.9
65°	15.8
67.5°	12.2
70°	8.5
72.5°	6.1
75°	4.9
77.5°	2.4
80°	2.4
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)