

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207061

Luminaire Tested: **LD4B30D010 EU4B30508027 4LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207061
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30508027 4LBWMW1
Description: PORTFOLIO 4 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2438.0 lumens
Efficiency: N/A
Efficacy: 87.1 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207061

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P207061

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78			
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69			
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61			
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55			
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	60	55	51	50			
7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45			
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41			
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38			
10	61	49	42	37	59	48	41	37	47	41	37	46	41	37	46	40	36	35			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207061

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.7	5.7
10°-20°	387.9	15.9
20°-30°	548.2	22.5
30°-40°	531.0	21.8
40°-50°	358.3	14.7
50°-60°	222.4	9.1
60°-70°	148.6	6.1
70°-80°	81.3	3.3
80°-90°	21.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1074.8	44.1
0°-40°	1605.8	65.9
0°-60°	2186.5	89.7
0°-90°	2438.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2438.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1477	
5°	1465	139
15°	1376	388
25°	1202	548
35°	854	531
45°	459	358
55°	244	222
65°	149	149
75°	76	81
85°	19	22
90°	0	



TEST NUMBER: P207061

CATALOG NUMBER: LD4B30D010 EU4B30508027 4LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1477.4
2.5°	1477.4
5°	1464.7
7.5°	1448.9
10°	1429.9
12.5°	1410.9
15°	1376.1
17.5°	1347.7
20°	1300.2
22.5°	1252.8
25°	1202.1
27.5°	1132.5
30°	1056.6
32.5°	958.5
35°	854.1
37.5°	749.8
40°	645.4
42.5°	541.0
45°	458.7
47.5°	382.8
50°	325.8
52.5°	278.4
55°	243.6
57.5°	215.1
60°	193.0
62.5°	170.8
65°	148.7
67.5°	129.7
70°	110.7
72.5°	94.9
75°	75.9
77.5°	60.1
80°	44.3
82.5°	31.6
85°	19.0
87.5°	6.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)