

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207338

Luminaire Tested: **LD4B10D010 EU4B10209030 4LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207338
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10209030 4LBMGPH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 495.0 lumens
Efficiency: N/A
Efficacy: 50.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.92
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207338

CATALOG NUMBER: LD4B10D010 EU4B10209030 4LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P207338

CATALOG NUMBER: LD4B10D010 EU4B10209030 4LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	88	86			
3	102	95	90	86	100	93	89	85	91	87	83	88	85	82	86	83	81	79			
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73			
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68			
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63			
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59			
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			
9	73	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	52	51			
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	53	49	48			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207338

CATALOG NUMBER: LD4B10D010 EU4B10209030 4LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.8	9.5
10°-20°	122.1	24.7
20°-30°	156.6	31.6
30°-40°	113.2	22.9
40°-50°	40.6	8.2
50°-60°	10.9	2.2
60°-70°	3.6	0.7
70°-80°	1.1	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	325.6	65.8
0°-40°	438.8	88.7
0°-60°	490.4	99.1
0°-90°	495.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	495.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	509	
5°	500	47
15°	435	122
25°	346	157
35°	181	113
45°	49	41
55°	11	11
65°	3	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P207338

CATALOG NUMBER: LD4B10D010 EU4B10209030 4LBMGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	509.0
2.5°	506.9
5°	499.6
7.5°	488.2
10°	472.6
12.5°	454.9
15°	435.1
17.5°	415.3
20°	395.5
22.5°	372.6
25°	345.6
27.5°	314.3
30°	274.8
32.5°	229.0
35°	181.1
37.5°	137.4
40°	99.9
42.5°	70.8
45°	48.9
47.5°	33.3
50°	21.9
52.5°	15.6
55°	11.4
57.5°	8.3
60°	6.2
62.5°	5.2
65°	3.1
67.5°	2.1
70°	2.1
72.5°	1.0
75°	1.0
77.5°	1.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)