

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207956

Luminaire Tested: **LD4B10D010 EU4B10209030 4LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207956
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10209030 4LBNMW1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 654.2 lumens
Efficiency: N/A
Efficacy: 66.1 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.95
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207956

CATALOG NUMBER: LD4B10D010 EU4B10209030 4LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P207956

CATALOG NUMBER: LD4B10D010 EU4B10209030 4LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	105	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			
3	98	90	84	80	96	89	83	79	86	82	78	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	78	73	69	76	72	68	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	62	57	53	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	53	49	58	53	49	48			
9	69	58	51	46	68	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	48	43	64	54	47	43	53	47	43	52	47	43	51	46	43	41			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207956

CATALOG NUMBER: LD4B10D010 EU4B10209030 4LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.3	7.8
10°-20°	134.3	20.5
20°-30°	176.8	27.0
30°-40°	137.6	21.0
40°-50°	66.8	10.2
50°-60°	42.2	6.5
60°-70°	27.2	4.2
70°-80°	14.2	2.2
80°-90°	3.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	362.5	55.4
0°-40°	500.1	76.4
0°-60°	609.2	93.1
0°-90°	654.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	654.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	558	
5°	548	51
15°	479	134
25°	390	177
35°	220	138
45°	83	67
55°	47	42
65°	27	27
75°	14	14
85°	3	4
90°	0	



TEST NUMBER: P207956

CATALOG NUMBER: LD4B10D010 EU4B10209030 4LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	558.1
2.5°	555.0
5°	547.7
7.5°	535.2
10°	518.6
12.5°	499.9
15°	479.1
17.5°	457.3
20°	434.4
22.5°	412.6
25°	389.7
27.5°	360.6
30°	321.1
32.5°	274.4
35°	220.3
37.5°	170.4
40°	132.0
42.5°	102.9
45°	83.1
47.5°	67.6
50°	59.2
52.5°	53.0
55°	46.8
57.5°	41.6
60°	36.4
62.5°	31.2
65°	27.0
67.5°	23.9
70°	19.7
72.5°	16.6
75°	13.5
77.5°	10.4
80°	7.3
82.5°	5.2
85°	3.1
87.5°	1.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)