

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207175

Luminaire Tested: **LD4B30D010 EU4B30509727 4LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P207175
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B30D010 EU4B30509727 4LBMH1
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1567.3 lumens
Efficiency: N/A
Efficacy: 56.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P207175

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P207175

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79			79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73			73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67			67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62			62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58			58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47			47

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P207175

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.0	9.1
10°-20°	375.1	23.9
20°-30°	482.1	30.8
30°-40°	362.7	23.1
40°-50°	145.7	9.3
50°-60°	41.4	2.6
60°-70°	13.1	0.8
70°-80°	3.8	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1000.3	63.8
0°-40°	1363.0	87.0
0°-60°	1550.1	98.9
0°-90°	1567.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1567.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1554	
5°	1526	143
15°	1339	375
25°	1064	482
35°	582	363
45°	180	146
55°	43	41
65°	12	13
75°	2	4
85°	0	0
90°	0	



TEST NUMBER: P207175

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1554.0
2.5°	1544.6
5°	1525.6
7.5°	1490.2
10°	1445.2
12.5°	1390.8
15°	1338.8
17.5°	1279.6
20°	1215.8
22.5°	1147.2
25°	1064.4
27.5°	965.1
30°	849.2
32.5°	719.1
35°	581.9
37.5°	454.1
40°	340.6
42.5°	250.7
45°	179.8
47.5°	123.0
50°	85.2
52.5°	59.1
55°	42.6
57.5°	30.7
60°	23.7
62.5°	16.6
65°	11.8
67.5°	9.5
70°	7.1
72.5°	4.7
75°	2.4
77.5°	2.4
80°	2.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)