

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205788

Luminaire Tested: **LD4B10D010 EU4B10209030 4LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205788
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD4B10D010 EU4B10209030 4LBSWH1
Description: PORTFOLIO 4 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 905.6 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205788

CATALOG NUMBER: LD4B10D010 EU4B10209030 4LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P205788

CATALOG NUMBER: LD4B10D010 EU4B10209030 4LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67			
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205788

CATALOG NUMBER: LD4B10D010 EU4B10209030 4LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.8	5.5
10°-20°	128.9	14.2
20°-30°	168.6	18.6
30°-40°	178.6	19.7
40°-50°	166.6	18.4
50°-60°	126.1	13.9
60°-70°	68.3	7.5
70°-80°	18.3	2.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	347.4	38.4
0°-40°	526.0	58.1
0°-60°	818.7	90.4
0°-90°	905.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	905.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	540	
5°	532	50
15°	461	129
25°	367	169
35°	285	179
45°	217	167
55°	142	126
65°	68	68
75°	16	18
85°	0	0
90°	0	



TEST NUMBER: P205788

CATALOG NUMBER: LD4B10D010 EU4B10209030 4LBSWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	540.1
2.5°	538.1
5°	532.1
7.5°	519.3
10°	502.4
12.5°	482.6
15°	460.8
17.5°	436.0
20°	414.2
22.5°	389.4
25°	366.7
27.5°	343.9
30°	322.1
32.5°	303.2
35°	285.4
37.5°	267.6
40°	250.7
42.5°	233.9
45°	217.0
47.5°	198.2
50°	179.4
52.5°	160.5
55°	141.7
57.5°	121.9
60°	103.1
62.5°	85.2
65°	68.4
67.5°	52.5
70°	38.6
72.5°	26.8
75°	15.9
77.5°	6.9
80°	2.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)