

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P207587

Luminaire Tested: **LD4B30D010 EU4B30509727 4LBMMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P207587  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD4B30D010 EU4B30509727 4LBMMW1  
Description: PORTFOLIO 4 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W  
DL3-29.67W DLE-29.73W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1631.0 lumens  
Efficiency: N/A  
Efficacy: 58.3 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P207587

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBMMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P207587

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBMMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89		
2	104	98	92	88	102	96	91	87	93	89	85	89	86	83	87	84	81	80		
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71		
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	69	66	64		
5	85	75	67	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58		
6	80	69	62	56	78	68	61	56	66	60	56	65	59	55	63	59	55	53		
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49		
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45		
9	67	55	48	44	66	55	48	44	54	48	44	53	47	43	52	47	43	42		
10	63	52	45	41	62	51	45	41	51	45	40	50	44	40	49	44	40	39		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P207587

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBMMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	114.8	7.0
10°-20°	307.7	18.9
20°-30°	409.1	25.1
30°-40°	334.6	20.5
40°-50°	194.9	11.9
50°-60°	129.3	7.9
60°-70°	85.0	5.2
70°-80°	44.8	2.7
80°-90°	10.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	831.5	51.0
0°-40°	1166.1	71.5
0°-60°	1490.3	91.4
0°-90°	1631.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1631.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1238	
5°	1224	115
15°	1096	308
25°	898	409
35°	534	335
45°	246	195
55°	144	129
65°	85	85
75°	42	45
85°	10	11
90°	0	



TEST NUMBER: P207587

CATALOG NUMBER: LD4B30D010 EU4B30509727 4LBMMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1238.2
2.5°	1235.8
5°	1224.0
7.5°	1195.6
10°	1164.9
12.5°	1136.6
15°	1096.4
17.5°	1051.5
20°	1013.7
22.5°	961.7
25°	897.9
27.5°	829.4
30°	742.0
32.5°	638.0
35°	534.0
37.5°	439.5
40°	356.8
42.5°	293.0
45°	245.7
47.5°	207.9
50°	181.9
52.5°	160.7
55°	144.1
57.5°	127.6
60°	111.1
62.5°	99.2
65°	85.1
67.5°	73.2
70°	61.4
72.5°	52.0
75°	42.5
77.5°	33.1
80°	23.6
82.5°	16.5
85°	9.5
87.5°	2.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)